

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL DRAWING	18OCT2021	TL	HL

D

C

B






A

D


C

B

A



RECOMMEND PCB-HOLE LAYOUT
COMPONENT SIDE SHOWN
TOLERANCE ±0.05



1 MATERIAL:
CONTACT: COPPER ALLOY.
HOUSING: GLASS-FILLED POLYESTER.

2 GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1.27μm MIN NICKEL AND ACTION
PIN: 0.5μm MIN TIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.

3 CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 2.

4 CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.

	2392181-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI 27MAY2021	TE Connectivity Ltd.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0-PLG ± 1-PLG ± 2-PLG ± 3-PLG ± 4-PLG ± ANGLES ±	CHK ALEX XU 27MAY2021		
	SEE TABLE	APVD HOPE LU 27MAY2021	NAME MALE ASSEMBLY, Z-PACK 2mm HM, 125P TYPE A/B EON	
		PRODUCT SPEC 108-19082	SIZE A1	
MATERIAL 		APPLICATION SPEC 114-160149	CAGE CODE 00779	DRAWING NO 2392181
		WEIGHT 0	RESTRICTED TO —	
		CUSTOMER DRAWING		SCALE 4:1
		SHEET 1 OF 1		REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2392181-1](#)