


Development of Small Lithium Ion Rechargeable Battery “SLB” Suitable for IoT and Wearable Applications


Small Lithium Ion Rechargeable Battery that achieves both high Power density and Energy density

Development Background



Product Features

- Rapid charging/discharging is possible: Support for 20 C rate rapid charging/discharging
- Low temperature performance: Possible to charge and discharge even in cold regions (-30°C)
- Safety: Extremely low explosion and ignition possibility even if an internal short circuit is forcibly generated
- Long life: Maintains a capacity of 80% or more after 25,000 charging/discharging cycles
 [Conditions] Temperature:25°C / Voltage range:1.8 to 2.8V
 Charging/discharging rate:10 C / Rest:0sec



Small Lithium Ion Rechargeable Battery SLB series

Specifications



Item	Characteristics
Nominal voltage	2.4V
Max. charge voltage (Under continuous charge)	2.8V
Discharge cutoff voltage (Under continuous discharge)	1.8V
Temperature range	-30 to 60°C

Part number	NEW SLB03070LR35	TENTATIVE SLB08115L140	TENTATIVE SLB12400L151
Size (mm)	φ 3×7L	φ 8×11.5L	φ 12.5×40L
Capacity (mAh)	0.35	14	150
Energy density (Wh/L)	17	58	73
Weight (g)	0.2	1.5	9.2

Features of Small Lithium Ion Rechargeable Battery "SLB"



1 Long life

Maintains a capacity of at least 80% after 25,000 charging/discharging cycles





2 Rapid charge/discharge

High input/output density approaching electric double layer capacitors (EDLCs)



3 Low temperatures

Possible to use in cold regions (-30deg.C)



4 Safety

Extremely low possibility of explosion or ignition even when used under harsh conditions

Extremely low risk of rupture or ignition and high safety.



Safe

Safety Test

Crushing by pressure



Nail penetration



NICHICON CORPORATION

HEAD OFFICE
NICHICON (AMERICA) CORP.
NICHICON (AUSTRIA) GmbH
NICHICON (HONG KONG) LTD.
NICHICON (SINGAPORE) PTE. LTD.
NICHICON (THAILAND) CO., LTD.
NICHICON ELECTRONICS (INDIA) PVT. LTD.
NICHICON CORPORATION KOREA REPRESENTATIVE OFFICE

URL <http://www.nichicon.co.jp/english>

TEL.81-75-231-8461 FAX.81-75-256-4158
 TEL.1-847-843-7500 FAX.1-847-843-2798
 TEL.43-1-706-7932 FAX.43-1-706-7933
 TEL.852-2363-4331 FAX.852-2764-1867
 TEL.65-6481-5641 FAX.65-6481-6485
 TEL.66-2-670-0150 FAX.66-2-670-0153
 TEL.91-80-4094-8661 FAX.91-80-4094-8651
 TEL.82-31-8065-6366 FAX.82-31-8065-6367

※ The data provided is for introduction purposes and is not guaranteed value.



SAFETY PRECAUTIONS

- Please use this product in accordance with NICHICON's product specifications. If the customer uses this product in a manner other than indicated in the delivery specifications, NICHICON will not assume responsibility in the event of failure.

NOTES

- SPECIFICATION AND DIMENSIONS IN THIS CATALOG ARE SUBJECT TO CHANGE WITHOUT NOTICE. IF NECESSARY, DRAWINGS CAN BE PROVIDED.
- OTHER THAN THE EXPRESS WRITTEN DELIVERY SPECIFICATIONS CONTAINED IN NICHICON'S CATALOG OR OTHER NICHICON LITERATURE, NICHICON MAKES NO WARRANTY, EXPRESS, IMPLIED, OR OTHERWISE, IN CONNECTION WITH THESE PRODUCTS, AND ALL IMPLIED WARRANTIES, INCLUDING THE WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PRODUCT, ARE DISCLAIMED. NICHICON SHALL NOT BE LIABLE FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES. CUSTOMER'S SOLE REMEDY IN THE EVENT THAT NICHICON'S DELIVERY SPECIFICATIONS ARE NOT MET IS TO REPAIR, REPLACE, OR REFUND THE PURCHASE PRICE OF THE SUBJECT PRODUCT, AT NICHICON'S OPTION.
- CATALOG PRINTED IN October 2019